



**SERIES 628
ADAPTERS / CABLE ASSEMBLIES**

ORDERING GUIDE

628 - 000 - 924

SERIES

EDAC INTERNAL

PRODUCT TYPE

SERIES

628 Series

PRODUCT TYPE

- 921 DVI / HD 15 cable assembly
- 922 LFH60 / HD 15 cable assembly
- 923 LFH60 / DVI cable assembly
- 924 DVI / HD 15 adapter
- 924S DVI / HD15 adapter - short black
- 924W DVI / HD15 adapter - short white
- 932 USB A / USB B cable assembly
- 935 RJ11 cable assembly
- 936 RJ45 cable assembly
- 937 SMB / SMB cable assembly
- 940 USB A / mini USB B cable assembly
- 944 USB B / USB B cable assembly
- 945 BNC / SMB cable assembly
- 953 Serial internal cable assembly
- 954 Multiple video cable assembly
- 955 LFH60 / 6XBNC cable assembly
- 957 LFH60 / 4XSCART cable assembly

FEATURES

- DVI - analog to 15 pin VGA adapter
- High cycle, dual beam low insertion force contacts
- D- subminiature adapting end is polarized
- Fully shielded to protect against EMI / RFI
- 4-40 threaded insert with thumbscrew
- Available in both long and short versions

SPECIFICATIONS

- Insulator material: UL94V-0 thermoplastic polyester
- Shell material: Nickel or tin plated steel
- Current rating: 1.5 amperes
- Dielectric withstanding voltage: 500V for 10 milliseconds
- Insulator resistance: 1000 Megohms at 100V DC
- Voltage: 40 V
- Impedance: 75 Ohms +/- 10% on co-axial wires

*For a more complete listing of products, please contact edac@edac.net