



PART NUMBER	MOUNTING-CLIP FOR PIPE O.D. Ø
ERP10074-XXX-X-01-XXXX	0.250"
ERP10074-XXX-X-02-XXXX	0.312"
ERP10074-XXX-X-03-XXXX	0.375"
ERP10074-XXX-X-04-XXXX	0.500"
ERP10074-XXX-X-05-XXXX	0.625"
ERP10074-XXX-X-06-XXXX	0.750"
ERP10074-XXX-X-07-XXXX	0.875"
ERP10074-XXX-X-08-XXXX	1.000"
ERP10074-XXX-X-09-XXXX	1.250"
ERP10074-XXX-X-10-XXXX	2.000"
ERP10074-XXX-X-11-XXXX	NO CLIP

SPECIFICATIONS:

RTD ELEMENT TCR = 3,850 ppm/°C
 MAXIMUM TEMPERATURE RATING = +105°C
 MOISTURE RESISTANT PROBE ASSEMBLY
 ROHS COMPLIANT

DIM "L"	TOLERANCE
<6.0"	± 0.500"
6.0" TO <12.0"	± 0.750"
12.0 TO 25.0"	± 6%
>25.0"	± 4%

REV	DESCRIPTION	DATE	APP
1	ADDED WIRE LENGTH OPTION	06/29/2020	DD
0	INITIAL RELEASE	06/24/2020	DD

REVISION HISTORY

EI SENSOR TECHNOLOGIES www.ei-sensor.com © COPYRIGHT	RTD PROBE	
	DRAWN BY: DAN DANKERT	
P/N ERP10074-	SCALE: NONE	LAYER: 0 OF 2
	REV: 1	DATE: 06/24/2020

This PROPRIETARY document is the property of EI Sensor Technologies. It is confidential in nature, non-transferrable and issued with the understanding that it is not to be traced or copied without permission, and is returnable on demand.

ERP10074-XXX-X-XX-XXXX

