

Datasheet

Art.No. 76.352.0760.5

Hood MIN GOT GB 7 M20 25 P5

revos MINI size 3 hood with cable gland M20 IP 68, top cable entry, single locking lever, plastic housing



Art.No.	76.352.0760.5
EAN	4015573719583
Order unit	10 pieces

Approvals

Technical data

General

Nominal voltage	250
Housing material	Plastic
Colour	White
Surface	Untreated
Degree of protection (IP)	IP65
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	V0
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	3
Model	male
Locking mechanism	Single locking lever
Cable entry	Above
Type of cable	Gland nut
With cable screw gland	Yes
Thread size M	20
Hinged lid	No
EMC-version	No