

Datasheet

Item No. 80.020.2004.0

Solid state relay WRS-SSDC-60V5A

WRS-solid-state-relays DC, solid state relay not plugable, with LED, open module housing WEB 1002. 80x12,5mm (HxW), control voltage: 24V DC, output: 60 V DC/5A, please note, that the negative pole of the control side can be bridged to the neighboring module. These jumpers have to be ordered separately if required.



|            |               |
|------------|---------------|
| Item No.   | 80.020.2004.0 |
| EAN        | 4015573440845 |
| order unit | 10 Piece(s)   |

Approvals



Technical data

**General**

|                 |    |
|-----------------|----|
| Modular version | No |
|-----------------|----|

**Technical data**

|                            |                  |
|----------------------------|------------------|
| Connection type            | Screw connection |
| Min. connection voltage    | 3 V              |
| Max. connection voltage    | 60 V             |
| Rated operating current DC | 5 A              |
| Min. control voltage       | 24 V             |

**Dimensions**

|        |         |
|--------|---------|
| Depth  | 59 mm   |
| Width  | 12.5 mm |
| Height | 80 mm   |