

Datasheet

Item No. 81.000.6190.0



Switched-mode power supply WIPOS P3 24-40

wipos switched-mode power supply, nominal voltage: 24 V DC / 40A (setting range 22,5-28,5 V DC), sustained short-circuit protection, input voltage range: 340-575 V AC, 480-820 V DC, 3 phase, W x H x D: 275,8 x 125,9 x 118,2 mm

Item No.	81.000.6190.0
EAN	4049088058257
order unit	1 Piece(s)

Approvals



Technical data

General

ArticlePrice	udp_no_price
Connection type	Screw connection
Modular version	No
Mounting type, other	No
Mounting type, wall mounting	No
Rail mounting possible	Yes

Technical data

Power consumption	1043 VA
Power output	960 W
Type of output voltage	DC
Output voltage stabilized	Yes
Min. output voltage	22.5 V
Max. output voltage	28.5 V
Output current	40 A
Input voltage AC min.	340 V
Input voltage AC max.	575 V
Input voltage DC min.	480 V
Input voltage DC max.	820 V

Dimensions

Depth	119 mm
Width	276 mm
Height	126 mm