

Datasheet

Item No. 81.000.6302.0

Switched-mode power supply

wipos switched-mode power supply, nominal voltage: 12 V DC / 0,83 A, sustained short-circuit protection, input voltage range: 90-264 V AC / 120-375V DC, single phase, DIN rail mounted device
1 mod.



Item No.	81.000.6302.0
EAN	4049088106156
order unit	1 Piece(s)

Technical data

General

ArticlePrice	udp_no_price
Connection type	Screw connection
Modular version	Yes
Mounting type, other	No
Mounting type, wall mounting	No
Rail mounting possible	Yes

Technical data

Power output	10 W
Type of output voltage	DC
Output voltage stabilized	Yes
Output voltage	12 V
Primary voltage range	90 V
Min. input voltage	90 V
Max. input voltage	264 V
Output current	0.83 A

Dimensions

Depth	56.5 mm
Width	18 mm
Height	91 mm