

Datasheet

Item No. 81.000.6322.0

Switched-mode power supply

wipos switched-mode power supply, nominal voltage: 12 V DC / 2 A, (setting range 12-14 V DC) sustained short-circuit protection, input voltage range: 90-264 V AC / 120-375 V DC, single phase, DIN rail mounted device 2 mod



Item No.	81.000.6322.0
EAN	4049088106163
order unit	1 Piece(s)

Technical data

General

ArticlePrice	udp_no_price
Connection type	Screw connection
Modular version	Yes
Mounting type, other	No
Mounting type, wall mounting	No
Rail mounting possible	Yes

Technical data

Power output	24 W
Type of output voltage	DC
Output voltage stabilized	Yes
Output voltage	12 V
Primary voltage range	90 V
Min. input voltage	90 V
Max. input voltage	264 V
Output current	2 A

Dimensions

Depth	56.5 mm
Width	35 mm
Height	91 mm