

Datasheet

Item No. 81.000.6330.0

Switched-mode power supply WIPOS PB1 24-2.5

wipos switched-mode power supply, nominal voltage: 24 V DC / 2,5A, (setting range 24-28 V DC) sustained short-circuit protection, input voltage range: 90-264 V AC / 120-375 V DC, single phase, DIN rail mounted device 4 mod.



Item No.	81.000.6330.0
EAN	4049088081460
order unit	1 Piece(s)

Approvals



Technical data

General

ArticlePrice	udp_no_price
Connection type	Screw connection
Modular version	Yes
Mounting type, other	No
Mounting type, wall mounting	No
Rail mounting possible	Yes

Technical data

Power output	60 W
Type of output voltage	DC
Output voltage stabilized	Yes
Min. output voltage	24 V
Max. output voltage	28 V
Output current	2.5 A
Input voltage AC min.	90 V
Input voltage AC max.	264 V
Input voltage DC min.	120 V
Input voltage DC max.	375 V

Dimensions

Depth	56.5 mm
Width	71 mm
Height	91 mm