

Datasheet

Art.No. 73.354.0635.1

Hood BAS GOT GI 6HM32 69 A1

revos BASIC 500V size 6H hood with threaded collar M32, top cable entry, high design, single locking lever



Art.No.	73.354.0635.1
EAN	4015573844223
Order unit	1 pieces

Approvals

Technical data

General

Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	6
Model	male
Locking mechanism	Single locking lever
Cable entry	Above
Type of cable	Thread
With cable screw gland	No
Thread size M	32
Thread size PG	
Hinged lid	No
EMC-version	No

Classification

ECLASS 8.1	27440202
ETIM 6.0	EC000437
ETIM 5.0	EC000437
ETIM 4.0	EC000437

ETIM 3.0

EC000437

