


Datasheet

Art.No. Z7.280.7327.0

Jumper bar IVBWKF 2,5 - 13



Art.No.	Z7.280.7327.0
EAN	4015573360235
Order unit	20 pieces

Approvals

ATEX SEV-Ex

Technical data

General

Colour	Yellow
Type	Cross connector
Modular spacing	5 mm
Number of bridged clamps	13
Mounting method	Pluggable
Insulated	Yes

Accessories

Type	Cross connector
Mounting method	Pluggable
Insulated	Yes
Colour	Yellow
Number of bridged clamps	13
Modular spacing	5 mm

Classification

ECLASS 8.1	27141140
ETIM 6.0	EC000489
ETIM 5.0	EC000489
ETIM 4.0	EC000489
ETIM 3.0	EC000489

Drawings

**10-polige Ausführung
10 poles variant**

PA 66
UL 94 V-2

These dimensions will be especially checked at delivery
Only inspection dimensions
NUR FÜR INSPEKTIONSDIMENSIONEN VERWENDBAR

These dimensions will be especially checked at delivery
Only inspection dimensions
NUR FÜR INSPEKTIONSDIMENSIONEN VERWENDBAR

These dimensions will be especially checked at delivery
Only inspection dimensions
NUR FÜR INSPEKTIONSDIMENSIONEN VERWENDBAR

Teile-Nr. part nr.	Pol- zahl poles	L-0.2	l±0,05	Typ type
27.280.62MM.0	2			IVBWK 2.5 - 2
27.280.63MM.0	3	14.8	10	IVBWK 2.5 - 3
27.280.64MM.0	4	19.8	15	IVBWK 2.5 - 4
27.280.65MM.0	5	24.8	20	IVBWK 2.5 - 5
27.280.66MM.0	6	29.8	25	IVBWK 2.5 - 6
27.280.67MM.0	7	34.8	30	IVBWK 2.5 - 7
27.280.68MM.0	8	39.8	35	IVBWK 2.5 - 8
27.280.69MM.0	9	44.8	40	IVBWK 2.5 - 9
27.280.70MM.0	10	49.8	45	IVBWK 2.5 - 10
27.280.71MM.0	11	54.8	50	IVBWK 2.5 - 11
27.280.72MM.0	12	59.8	55	IVBWK 2.5 - 12
27.280.73MM.0	13	64.8	60	IVBWK 2.5 - 13
27.280.74MM.0	14	69.8	65	IVBWK 2.5 - 14
27.280.75MM.0	15	74.8	70	IVBWK 2.5 - 15
27.280.76MM.0	16	79.8	75	IVBWK 2.5 - 16
27.280.77MM.0	17	84.8	80	IVBWK 2.5 - 17
27.280.78MM.0	18	89.8	85	IVBWK 2.5 - 18
27.280.79MM.0	19	94.8	90	IVBWK 2.5 - 19
27.280.80MM.0	20	99.8	95	IVBWK 2.5 - 20

Weitere Daten siehe Katalog
further data see catalog

MM	
27	Katalogteil catalogue part
97	spezielle Verpackung special packing

Tolerierung Size ISO 14405/Tolerance system Size ISO 14405
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☑ Stoffverbots- und Deklarationsliste nach DIN 5020:2010 ist einzuhalten.
Conformity with Wieland document MW 5030.003 = (List of prohibited /
declarable hazardous substances) to be declared!

Freitoleranz nach
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung:
First Use:

Blatt: 1 von 1
Sheet: 1 of 1

/	Workstoff/Material	2001	Tag/Date	Name	Zeichnung Nr./Drawing No.	Index
/		gezeichnet drawn	04.07.	TRESCHM	27.280.6227.0 01K b	b
/	Maßstab/Scale	geprüft checked	-	-		
/	2:1	Skizzen- Stand. check	-	-		
/	Vol.	mm	Off./Surf.	mm	Ersatz für/Replacement for:	

www.wieland-electric.com

Typ
IVB WK
2,5 - ..

Benennung/Titel
VERBINDUNGSSTECKER
insulated jumper bar

Z72806227001K_2 CADW302B Treschm 2015-12-15T15:30:54z 1.000

3 QU-MEE-01/14