

Datasheet


Art.No. 80.010.6132.2

Relay module FLARE MR 24VDC-2W-8A-F



Art.No.	80.010.6132.2
EAN	4049088034886
Order unit	10 pieces

Approvals



Technical data

General

Connection type	Tension clamp connection
Number of change-over contacts	2
Detachable clamps	No
Drive, polarization	Polarized
Drive, function	Mono stable
Forced-guided contacts	No
Complete with socket	Yes
Degree of protection (IP)	IP20

Technical data

Type of excitation	DC
Min. rated DC voltage for controls	17.52 V
Max. rated DC voltage for controls	26.4 V
Nominal voltage DC	24 V
Lower nominal voltage DC	17.52 V
Upper nominal voltage DC	26.4 V

Other

Contact material	AgNi
------------------	------

Dimensions

Depth	68.1 mm
Width	15.8 mm

Height	82.9 mm
--------	---------

**Classification**

ECLASS 8.1	27371601
ETIM 6.0	EC001437
ETIM 5.0	EC001437
ETIM 4.0	EC001437
ETIM 3.0	EC001437