

Datasheet

Art.No. 83.040.0000.0

IP switch WIENET UMS 6

wieNET IP Switch, 6 TP-RJ45-Ports, transfer rate 10/100 MBit/s, unmanaged switch, Autonegotiation, Autosensing, Autocrossing-function, redundant power supply, supply voltage: 9-30 V, vertical mount



Art.No.	83.040.0000.0
EAN	4049088081927
Order unit	1 pieces

Approvals



Technical data

Allgemein

Mounting method	DIN rail (top hat rail)
Degree of protection (IP)	IP50
Diagnostic LEDs	Power/Link status/Data/Data rate
Ethernet	Yes
Power over Ethernet	No
Fast Ethernet	Yes
Gigabit Ethernet	No
Number of ports 10/100 Mbps RJ45	6
10 Gigabit Ethernet	No
Number of ports 10/100/1000 Mbps RJ45	0
Number of ports 100 Mbps SC	0
Number of 100 Mbps ST-Ports	0

Technical data

Voltage type	DC
Min. operating temperature	-10 °C
Max. operation temperature	60 °C
Operating voltage min.	9 V
Operating voltage max.	30 V
Redundant power supply	2 power inputs

Dimensions

Depth	80 mm
-------	-------

Width	45 mm
Height	91 mm