

Datasheet

Item No. R1.180.0070.0

PLC digital I/O-module SA-IN-S1-K-A DC 24V (A)

samos input module, programming by switch, 2x4 inputs, 2x10 input functions, coding 1, pluggable terminals screws



Item No.	R1.180.0070.0
EAN	4015573818064
order unit	1 Piece(s)

Approvals



Technical data

General

SIL according to IEC 61508	3
SIL according to IEC 62061	3
Category according to EN 954-1	4
In-/outputs configurable	Yes
Performance level acc. to EN ISO 13849-1	e

Connection Data

Type of electric connection	Screw connection
-----------------------------	------------------

Output circuit

Number of outputs	0
-------------------	---

Other

Suited for safety functions	Yes
-----------------------------	-----

Control circuit

Number of inputs	8
"Input current (at state ""1"")"	8 mA
Permitted voltage at input	30 V

Supply circuit

Min. supply voltage at DC	19.2 V
Max. supply voltage at DC	30 V

Dimensions

Depth	121 mm
Width	22.5 mm

Height	96.5 mm
--------	---------