

Datasheet

Item No. R1.180.0080.0

PLC digital I/O-module SA-OR-S1-4RK-A DC 24V (A)

samos output module, 2x2 enabling current paths 2x2 signalling output, DC 24 V, pluggable terminals screws



Item No.	R1.180.0080.0
EAN	4015573818071
order unit	1 Piece(s)

Approvals



Technical data

General

SIL according to IEC 61508	3
SIL according to IEC 62061	3
Category according to EN 954-1	4
In-/outputs configurable	Yes
Performance level acc. to EN ISO 13849-1	e

Connection Data

Type of electric connection	Screw connection
-----------------------------	------------------

Output circuit

Number of outputs	6
Output current	6 A
Short-circuit protection, outputs	No
Type of digital output	Relay
Min. allowed output voltage	5 V
Max. allowed output voltage	230 V

Other

Suited for safety functions	Yes
-----------------------------	-----

Control circuit

Number of inputs	0
------------------	---

Supply circuit

Min. supply voltage at DC	19.2 V
Max. supply voltage at DC	30 V

Dimensions

Depth	121 mm
Width	22.5 mm
Height	96.5 mm