

Datasheet

Item No. Z5.507.4821.0

EMC cable gland M20x1,5

Cable gland EMC IP 68 M20x1,5, metal



Item No.	Z5.507.4821.0
EAN	4015573631519
order unit	1 Piece(s)

Technical data

General

Thread size M	20
Thread length	6 mm
Min. cable diameter	8 mm
Max. cable diameter	13 mm
Degree of protection (IP)	IP68
Material	Brass
Surface	Nickel-plated
Colour	Other
Wrench width	22 mm
Shock resistant	Yes
Bend radius protection/trumpet flare	No
Cross bracket strain relief	No
Type of sealing	Cut-out ring
Separable screw gland	No
Multi seal area	No
Thread type	Metric
Halogen free	Yes
Inflammability class of insulation material acc. with UL94	Other