

## 200A AC/DC Mini Clamp Meter

 **Economical clamp-on for AC Current measurements to 10mA and DC Current to 100mA**  
With overload protection to 300A

### Features:

- 0.75" (19mm) jaw opening (AWG 4)
- Low battery and overrange indication
- Bright 1/2" LCD (2000 count) display with Data Hold
- Complete with test leads, wrist strap, 9V battery and case



Specifications	Range	Resolution	Accuracy (%rdg+digits)
AC Current	20A/200A	0.01A/0.1A	±(1.2%FS + 5d)
DC Current	200A	0.1A	±(1.2%FS + 5d)
AC Voltage (40-400 Hz)	500V	1V	±(1% + 2d)
DC Voltage	200V	0.1V	±(0.8% + 1d)
Resistance	200Ω	0.1Ω	±(1.2% + 1d)
Zero Adjust	External knob for DCA		
Dimensions	7.1x1.9x1.4" (180x47x35mm)		
Weight	8oz (225g)		

### Ordering Information:

380652.....200A Mini DC/AC Clamp DMM  
380652-NIST .....200A Mini DC/AC Clamp DMM w/NIST Certificate  
480172.....AC Line Separator-3prong

