

## InfraRed ProbeMeter™

Pocket size InfraRed Thermometer measures up to 1022°F (550°C) with laser pointer and audible alarm

### Features:

- Large 2000 count (reads to 1022°F) multi-function backlit LCD
- Built-in laser pointer to improve aim and accuracy
- Adjustable Hi/Lo set points with audible beeper alarm to alert user when temperature exceeds the programmed set points
- Auto-hold after releasing the Measure button
- Adjustable emissivity (0.1 to 1.00)
- Narrow field of view (at 10" distance measure 1" target)
- Auto Power off
- Includes carrying case and 4 AAA batteries

### Applications:

- Measure surface temperature of objects difficult to reach or unsafe to contact
- Measure hot spots in electrical panels and equipment
- In-process temperature measurements



CE

Specifications	
Range:	-4 to 1022°F or -20 to 550°C
Accuracy:	±2% of reading or ±6°F or ±3°C (whichever is greater)
Resolution:	1°F/°C
Emissivity:	Adjustable from 0.1 to 1.00
Display:	Backlit LCD, 2000 counts
Power:	four 1.5V AAA batteries
Field of view:	10:1 (at 10" distance measure 1" target)
Dimensions:	6.7x1.7x1.6" (170x44x40mm)
Weight:	6.4oz (200g)

### Ordering Information:

403265 .....InfraRed ProbeMeter™ with Alarm  
403265-NIST .....InfraRed ProbeMeter™ with Alarm with NIST Certificate