

Flexible Borescope



Fiberscope Inspection tool

With built-in light source to illuminate viewed object

Features:

- High resolution image bundle and optical system
- Easy to use eyepiece and handle
- Focus adjustment
- Bright light to illuminate viewed object
- Flexible gooseneck retains configured shape
- Removable 90 degree side viewing adaptor rotates 360 degrees
- Can be exposed to water, diesel, gasoline, brake fluid, antifreeze, oil and other liquids
- Complete with 3 AA batteries and storage case

Applications:

- Home inspection: Inspect in walls for mold, insect infestation, electrical wire or water pipe location
- HVAC: Inspect inside ducts, behind motors and compressors
- Automotive: View inside or around engines and transmissions
- Government: Safety and security inspections
- Industrial: Inspect weld integrity, process equipment, gears, molding machines
- Aerospace: Aircraft inspections for contamination, debris, cracks or other damage



Specifications	
Viewing direction	0°; Viewing Angle 45°
Depth of observation	1 to 6" (30 to 150mm)
Side view adaptor	90°, Viewing Angle 45°
Shaft diameter	0.35" (9mm)
Working length	36" (914mm)
Weight	13oz (370g)
Carrying case dimensions	12.6 x 9.84 x 2.75" (320 x 250 x 70mm)

Ordering Information:

BR136.....Flexible Borescope (36" cable)

