



NOTES: UNLESS OTHERWISE SPECIFIED

1. CONSTRUCTION:
 HOUSING: MOLDED NYLON. AVAILABLE IN TEN COLORS
 FOOT HOUSING: MOLDED NYLON. RED
 CONTACT BLADE: BRIGHT DIP NICKEL SILVER
 SPRING: STAINLESS STEEL
 WASHER: HARD RED FIBER

2. PERFORMANCE:
 MAXIMUM CURRENT:
 MAXIMUM VOLTAGE: 33V AC/ 70V DC
 MAXIMUM TEMPERATURE: 200°F (93°C)

REVISIONS		DATE	APPROVED
LTR	DESCRIPTION		



ACTUAL SIZE

		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± ± .XXX ±	CONTRACT NO.		E-Z-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.	
			APPROVALS	DATE		
		MATERIAL SEE NOTE.	DRAWN	R.L.	3/19	
			APPROVED BY			
		FINISH SEE NOTE.			DESCRIPTION SUBSTITUTION TEST CLIP	
NEXT ASSY	USED ON				SIZE	CODE IDENT NO.
APPLICATION		DO NOT SCALE DRAWING			DRAWING NO.	REV.
					B 08505	71-1
					SCALE	3:1
					SHEET 1 OF 1	