

> [PN Search](#)

[Home page](#)

Product quick search

P/N Search

FCI Competitor

GO

RoHS/LF P/N Search

Product type search
 Alphabetical list
 Connection type
 Markets / Applications

[Product finder](#)

[Literature](#)

[Services](#)

[Contact us](#)

Registered users

[Forgot password ?](#)

[Register now](#)

Hood
8655MH2501



> Communications Data & Consumer division

FCI brings you more

[Contact our sales/technical support](#)

[Sample request](#)

€ [Price request](#)

[Check distributor stock](#)

[Download](#)

[Mating half](#)

[Alternative parts](#)

[Application tooling](#)

> [Customer Drawing](#)

Not Available

Not Available

www.foehrenbach.be
[Americas](#)
[Asia Pacific](#)

Features Selected

Orientation Straight

EMI /RFI performance Shielded

Material Metal

Total # of Positions 25

Packaging Bulk

Other Properties

Temperature Range -55°C to +125°C

Comments High performance hood

Pack factor 60

Shell Size B

Material characteristics Zamack with nickel plating

Product Type Hood

Attachment to: Cable