

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

10123196-300S050

10123196-300S050 - IOconnections : MiniSAS HD Active Optical Cable, OFNP, 50 meter, straight cable exit




MATURE

Distributor Stock

Print Datasheet

FCI Brings You More

[Contact our sales/technical support](#)
[Sample request](#)


Customer drawing



Product Environmental Compliance Report

Specifications

Download document

Mating Half

General Dimensional Electrical Mechanical Physical Approvals / Certifications Other Features

General

Cable Exit Style	straight
Fiber Type	OM3
Product Type	Active Optical Cable
Cable Colour	Aqua

Dimensional

Cable Length	50 meter
--------------	----------

Electrical

Power	0.8 Watts per end
Signal Speed	12 Gb/s per lane (4 lanes)
Power Supply Voltage	3.3V

Mechanical

Durability (Mating cycles)	50 Cycles
Insertion force (Plug contact)	40 N
Retention force (Plug contact)	90 N

Physical

Cable Type	Plenum (OFNP)
Temperature (Range)	-5°C to +70°C

Approvals / Certifications

Approvals / Certifications	UL, TUV and FDA Approved
UL File Number	E251142
TUV File Number	DE2-015589
FDA File Number	0312716-414

Other Features

Packaging (Type)	high shield ESD bubbly wrap bag
Literature	mini-sas-hd-aoc-datasheet.pdf

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.