

■ Combinations meeting for UL market

• **BM3RSB, BM3RHB, BM3RSR, BM3RHR**

3-phase motor				Manual motor starters		Adjustable current range (A)	Magnetic contactor	Link module	Base plate
Rated capacity (HP) 220-240V AC	Rated operational current (A)	Rated capacity (HP) 440-480V AC	Rated operational current (A)						
-	-	-	-	BM3RSB-P16	BM3RHB-P16	0.1 to 0.16	SC-M01	BZ0LRC09AA	*1 (BZ0BPVE22A)
							SC-E02	BZ0LRE22AA	BZ0BPVE22A
-	-	-	-	BM3RSB-P25	BM3RHB-P25	0.16 to 0.25	SC-M01	BZ0LRC09AA	*1 (BZ0BPVE22A)
							SC-E02	BZ0LRE22AA	BZ0BPVE22A
-	-	-	-	BM3RSB-P40	BM3RHB-P40	0.25 to 0.4	SC-M01	BZ0LRC09AA	*1 (BZ0BPVE22A)
							SC-E02	BZ0LRE22AA	BZ0BPVE22A
-	-	-	-	BM3RSB-P63	BM3RHB-P63	0.4 to 0.63	SC-M01	BZ0LRC09AA	*1 (BZ0BPVE22A)
							SC-E02	BZ0LRE22AA	BZ0BPVE22A
-	-	-	-	BM3RSB-001	BM3RHB-001	0.63 to 1.0	SC-M01	BZ0LRC09AA	*1 (BZ0BPVE22A)
							SC-E02	BZ0LRE22AA	BZ0BPVE22A
-	-	0.75	1.6	BM3RSB-1P6	BM3RHB-1P6	1.0 to 1.6	SC-M01	BZ0LRC09AA	*1 (BZ0BPVE22A)
							SC-E02	BZ0LRE22AA	BZ0BPVE22A
0.5	2.2	1	2.1	BM3RSB-2P5	BM3RHB-2P5	1.6 to 2.5	SC-M01	BZ0LRC09AA	*1 (BZ0BPVE22A)
							SC-E02	BZ0LRE22AA	BZ0BPVE22A
0.75	3.2	2	3.4	BM3RSB-004	BM3RHB-004	2.5 to 4	SC-M01	BZ0LRC09AA	*1 (BZ0BPVE22A)
							SC-E02	BZ0LRE22AA	BZ0BPVE22A
1.5	6	3	4.8	BM3RSB-6P3	BM3RHB-6P3	4 to 6.3	SC-M01	BZ0LRC09AA	*1 (BZ0BPVE22A)
							SC-E02	BZ0LRE22AA	BZ0BPVE22A
-	-	5	7.6	BM3RSB-010	BM3RHB-010	6.3 to 10	SC-M02	BZ0LRC09AA	*1 (BZ0BPVE22A)
							SC-E02	BZ0LRE22AA	BZ0BPVE22A
3	9.6	7.5	11	BM3RSB-013	BM3RHB-013	9 to 13	SC-E03	BZ0LRE22AA	BZ0BPVE22A
5	15.2	10	14	BM3RSB-016	BM3RHB-016	11 to 16	SC-E04	BZ0LRE22AA	BZ0BPVE22A
5	15.2	10	14	BM3RSB-020	BM3RHB-020	14 to 20	SC-E04	BZ0LRE22AA	BZ0BPVE22A
7.5	22	15	21	BM3RSB-025	BM3RHB-025	19 to 25	SC-E05	BZ0LRE22AA	BZ0BPVE22A
10	28	20	27	BM3RSB-032	BM3RHB-032	24 to 32	SC-E1	BZ0LRE32AA	BZ0BPVE32A

Note: *1 Use the base plate type in () when you use the base plate.

• **BM3VSB, BM3VHB**

3-phase motor				Manual motor starters		Adjustable current range (A)	Magnetic contactor	Link module	Base plate
Rated capacity (HP) 220-240V AC	Rated operational current (A)	Rated capacity (HP) 440-480V AC	Rated operational current (A)						
3	9.6	5	7.6	BM3VSB-010	BM3VHB-010	6.3 to 10	SC-E1	BZ0LVE51AA	BZ0BPVE51A
3	9.6	7.5	11	BM3VSB-013	BM3VHB-013	9 to 13	SC-E1	BZ0LVE51AA	BZ0BPVE51A
5	15.2	10	14	BM3VSB-016	BM3VHB-016	11 to 16	SC-E1	BZ0LVE51AA	BZ0BPVE51A
5	15.2	10	14	BM3VSB-020	BM3VHB-020	14 to 20	SC-E1	BZ0LVE51AA	BZ0BPVE51A
7.5	22	15	21	BM3VSB-025	BM3VHB-025	19 to 25	SC-E1	BZ0LVE51AA	BZ0BPVE51A
10	28	20	27	BM3VSB-032	BM3VHB-032	24 to 32	SC-E1	BZ0LVE51AA	BZ0BPVE51A
10	28	30	40	BM3VSB-040	BM3VHB-040	28 to 40	SC-E2	BZ0LVE51AA	BZ0BPVE51A
15	42	30	40	BM3VSB-050	BM3VHB-050	35 to 50	SC-E2S	BZ0LVE51AA	BZ0BPVE51A
20	54	40	52	BM3VSB-063	BM3VHB-063	45 to 63	SC-E3	BZ0LVE65AA	BZ0BPVE65A