



Search by model

[Specifications](#)

[Manual](#)

[Product registration](#)

[Accessories](#) > [Pressure](#) > [Dual pressure modules](#) >

## 700PD6 Dual Pressure Module (-1000 mbar/+6.9 bar)



- Display pressure readings in any of 10 different pressure units you specify in the calibrator setup
- Rugged urethane molded case protects the module from rough handling and harsh conditions
- Features internal temperature compensation from 0° C to 50° C for full-accuracy performance
- Includes NIST-traceable calibration certificate
- Module can be calibrated locally using the Fluke 700PCK Pressure Calibration Kit, a PC, and a precision pressure source
- One year warranty

\*Prices are suggested resale prices (excl. VAT)