

## Fluke TL175 TwistGuard™ Test Leads

Download manuals 

Quality test leads with adjustable length test tips for use in different measurement environments and increased safety. Buy Online Now.



### Related Products



[TP175 TwistGuard™ Test Probes »](#)



Fluke TL175 TwistGuard™ Test Leads CAT Ratings

[Overview](#) | [Features](#) | [Specifications](#) | [Models and Accessories](#) | [More Info](#)

Model Name	Description
TL175E	TL175E TwistGuard™ Test Leads with 4 mm lantern tips
TL175	TL175 TwistGuard™ Test Leads

## Fluke TL175 TwistGuard™ Test Leads

Download manuals 

Quality test leads with adjustable length test tips for use in different measurement environments and increased safety. Buy Online Now.



### Related Products



[TP175 TwistGuard™ Test Probes »](#)



Fluke TL175 TwistGuard™ Test Leads CAT Ratings

[Overview](#) | [Features](#) | [Specifications](#) | [Models and Accessories](#) | [More Info](#)

**Ratings:** CAT II 1000 V, CAT III 1000 V, CAT IV 600 V, 10 A max., Pollution Degree 2  
**Exposed probe tip length:** 19 mm to 4 mm (0.75 inch to 0.16 inch)  
**Environmental ratings:** -20 °C to 55 °C (-4 °F to 131 °F), altitude: 2000 m (6,562 ft)

TL175E also available. Includes removable 4 mm lantern tips that thread onto the lead tip.  
 Conforms to EN61010-031