



« Thermometers

## Fluke 61 IR Thermometer

Fluke 61 mini IR thermometer gives accurate readings over temperatures ranging from -40°C to 760°C with the enhanced optics for measurements in hard-to-reach and dangerous situations.

[Check Pricing/Buy Now](#)

5.0 (2)

[Write a review](#)

Manuals



[Overview](#)

[Features](#)

[Reviews](#)

**[Specs](#)**

[Models/Accessories](#)

[Resources](#)

### Specifications

<b>Backlit display for use in poorly lit areas</b>	Yes
<b>Holds temperature readings</b>	Yes
<b>Range</b>	-18 to 275°C (-0 to 525°F)
<b>MIN/MAX/AVG</b>	N/A
<b>Datalogging</b>	N/A
<b>Distance to spot ratio</b>	8:1
<b>Hi-Lo alarm</b>	N/A
<b>Optional RTD probe (contact temperature measurement)</b>	N/A
<b>Emissivity</b>	Fixed at 0.95
<b>Measurement Accuracy</b>	
<b>-18°C (0°F) to -1°C (30°F)</b>	±3°C (5°F)
<b>above -1°C (30°F) to 275°C (525°F)</b>	±2% of reading or 2°C (3.5°F) (With the instrument stable between 23-25°C)

### Product Registration

## Products

- [Buy Fluke Accessories](#)
- [Buy Factory Reconditioned](#)
- [Contests and Promotions](#)
- [Manuals](#)
- [New From Fluke](#)
- [Product Registration](#)
- [Test Tools Catalog](#)
- [Where to Buy](#)

## Company

- [About Us](#)
- [Awards](#)
- [Careers](#)
- [Companies](#)
- [Integrity](#)
- [Press](#)
- [Supplier Handbook](#)
- [Tax Information](#)

## Customer Service

- [Contact Us](#)
- [Directions](#)
- [Feedback](#)
- [Safety Notices](#)

**Fluke Newsletters Signup**



United States / English

- [Safety Notices](#)
- [Site Map](#)
- [Privacy Policy](#)
- [Fluke Terms of Use](#)
- [Fluke Terms & Conditions of Sale](#)

Copyright ©1995-2014 Fluke Inc.

[Back to top of page](#)