

United States [Change] | Fluke [Change]



Home Solution Centers Products Where To Buy Fluke Community Education & Training Support Services About Us

Home | Products | Accessories | Current Clamps |

Contact us

i1000s AC Current Probe

Available inventory Fluke store Download manuals



Search Fluke

Resources Products

Find Resources



Overview Features Specifications Models and Accessories Knowledge and Information

Specifications	
Nominal current range	10 A 100 A 1000 A
Continuous current range	0.1 A - 10 A 0.1 A - 100 A 1 A - 1000 A
Maximum Non-Destructive Current	2000 A
Lowest measurable current	0.1
Basic Accuracy	1% + 1 A (48-65 Hz) (% reading + floorspec)
Useable frequency	5 Hz - 100 kHz
Output level(s)	100 mv/A 10 mv/A 1 mv/A

Safety Specifications	
Safety	CAT III, 600 V CAT IV, 300 V
Maximum voltage	600 V AC

Mechanical & General Specifications	
Warranty	1 year
Maximum conductor diameter	54 mm
Output cable length	1.6 m
BNC Adapter	Yes