

Fluke VPS40-III Voltage Probe, 10:1, With Safety-Designed Shrouded 4mm Testpin



Specification

Attenuation	10x
Bandwidth	DC to 40 MHz (-3 dB)
Max input voltage	600 V CAT III / 1000 V CAT II as per IEC61010-031:2008
V*Hz product	500*10 ⁶ VHz
Max floating voltage	See instrument manual
Input resistance / Capacitance	5 MΩ / 15.5 pF
Compensation	Fixed for ScopeMeter 120 Series (14 pF)
Probe tip	Safety-shrouded 4 mm banana pin with test tip (see photo)
Instrument connector	4 mm shielded banana plug
Cable length	1.2 m