

GC PROFESSIONAL™ PLIERS AND CUTTERS



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7

GC Professional™ Pliers and Cutters

Retail Part No.	Bulk Part No.	Figure No.	Description	Overall Length	Nose Style	Pliers or Cutters Type
12-7301		1	Chain Nose	4.50"	Smooth	Pliers
12-7302		2	Chain Nose	5.00"	Smooth	Pliers
12-7303		3	Flat Nose	4.50"	Smooth	Pliers
12-7305		4	Round Nose	4.50"	Smooth	Pliers
12-7306		5	Round Nose	5.00"	Smooth	Pliers
12-7313		6	Extra Long Bent Nose	6.00"	Smooth	Pliers
12-7315		7	Long Nose Side Cutter	4.75"	Serrated	Pliers/Cutters

GC PROFESSIONAL™ PLIERS AND CUTTERS (Cont.)



Fig. 1



Fig. 2



Fig. 3

Tools

GC Professional™ Pliers and Cutters (Cont.)

Retail Part No.	Bulk Part No.	Figure No.	Description	Overall Length	Nose Style	Pliers or Cutters Type
12-7310		1	Bent Nose	4.50"	Serrated	Pliers
12-7322		2	Oval Head Cutter	5.00"	Semi-flush	Cutters
12-7324		2	Oval Head Cutter	5.00"	Flush	Cutters
12-7332		3	Mini Oval Head Cutter	4.50"	Flush	Cutters

PLIERS AND CUTTERS



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7



Fig. 8



Fig. 9



Fig. 10



Fig. 11

Palm Grip Pliers

Retail Part No.	Bulk Part No.	Figure No.	Description	Handle Color	Nose Style	Features
12-200		1	Flush Cutter	Red	Flush	
12-204		2	Flat Nose Pliers	Blue	Serrated	
12-208		3	Flat Nose Pliers	White	Non-serrated	
12-212		4	Round Nose Pliers	Yellow	Smooth	
12-216		5	Needle Nose Pliers	Green	Smooth	
12-220		6	Curved Nose Pliers	Orange	Smooth	
12-7070		7	5-piece Precision Pliers Set	Black	Smooth	Includes Micro Snub, Flat, Round, Bent Nose and Long Nose Pliers
12-7071		8	Micro Flat Nose Pliers	Black	Smooth	Perfect for Minimal Jaw Thickness
12-7072		9	Micro Snub Nose Cutting Nipper	Black	Cutter	Ideal for Trimming
12-7073		10	Micro Round Nose Pliers	Black	Smooth	Holds Tiny Wires
12-7075		11	Micro Bent Nose Pliers	Black	Smooth	Reaches/Holds Under PC Boards

PLIERS AND CUTTERS (Cont.)



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6

Pliers and Cutters

Retail Part No.	Bulk Part No.	Figure No.	Description	Handle Color	Overall Length	Nose Style	Weight (Pounds)
12-300		1	Mini Diagonal Cutting Pliers	Orange	4.00"		0.16
12-306		1	Mini Diagonal Cutting Pliers	Orange	4.50"		0.16
12-312		2	Narrow Diagonal Cutting Pliers	Orange	5.00"		0.22
12-318		3	High Leverage Diagonal Cutting Pliers	Orange	7.00"		0.56
12-500		4	Flush Cutters	Orange	5.00"		
12-504		5	Clip/Grip Flush Cutter	Orange	4.50"		
12-1950		6	Snap Ring Plier Kit	Red	6.50"		



Fig. 7

Precision Electronic Screwdrivers

Retail Part No.	Bulk Part No.	Figure No.	Description	Blade Size	Shaft Diameter	Shaft Length	Handle Length	Overall Length
12-6114		7	Flat Head Screwdriver	1.4 mm	2.0 mm	40 mm	S-80 mm	120 mm
12-6120		7	Flat Head Screwdriver	2.0 mm	2.0 mm	40 mm	S-80 mm	120 mm
12-6220		7	Flat Head Screwdriver	2.0 mm	2.0 mm	75 mm	M-95 mm	170 mm
12-6224		7	Flat Head Screwdriver	2.4 mm	2.4 mm	75 mm	M-95 mm	170 mm
12-6225		7	Flat Head Screwdriver	2.4 mm	2.4 mm	100 mm	M-95 mm	195 mm
12-6330		7	Flat Head Screwdriver	3.0 mm	3.0 mm	100 mm	L-105 mm	205 mm
12-6341		7	Flat Head Screwdriver	4.0 mm	4.0 mm	150 mm	L-105 mm	255 mm