

## TOOLS FOR ELECTRONIC APPLICATIONS




Fig. 1




Fig. 2




Fig. 3

### Universal Solderless Terminal Crimping Tool and Bolt Cutters

Retail Part No.	Figure No.	Crimps Terminals	Cuts/Strips Wire	Wire Range	Cuts Bolts (Sizes)	Overall Length	Handle Color
CT-4071-P	1	Ring, Flanged Spade, Spade Terminal, Butt Slices, Closed End Connectors	Yes	10-25 AWG	4-40, 6-32, 8-32, 10-24, 10-32	8.25 in.	Red

### Terminal Crimper Red

Retail Part No.	Figure No.	Crimps Terminals	Cuts/Strips Wire	Wire Range	Cuts Bolts (Sizes)	Overall Length	Handle Color
W-HT-1919-P	2	.093" Pin Diameter Terminals, Standard KK Crimp Terminals for .156" Center KK Housings, Series #1189/1190, Series #1380/1381, Series #2478	Yes	14-24 AWG	4-40, 6-32, 8-32, 10-24, 10-32	8.25 in.	Red

### Terminal Crimper Yellow

Retail Part No.	Figure No.	Crimps Terminals	Cuts/Strips Wire	Wire Range	Cuts Bolts (Sizes)	Overall Length	Handle Color
W-HT-1921-P	3	.062" Pin Diameter Terminals, .093" Pin Diameter Terminals, Mini KK Terminals for .100" Center KK Housings, Standard KK Crimp Terminals for .156" Center KK Housings, Series #1433/1434, Series #1560/1561, Series #1854/1855, Series #2759, Series #2578	Yes	18-30 AWG	4-40, 6-32, 8-32, 10-24, 10-32	8.25 in.	Yellow