



Select a Language



Supplier Center Distributor Center

BROWSE PRODUCTS

Category: | Browse by Brand:

PRODUCTS

- [Bending](#)
- [Bolt Cutters](#)
- [Cable Termination](#)
- [CATV/Broadband Instruments](#)
- [Connectors](#)
- [Electric Test Instruments](#)
- [Fasteners](#)
- [Fiber Connections](#)
- [Fiber Optic Instruments](#)
- [Fishing](#)
- [Hydraulic Tools](#)
- [Knockout Sets](#)
- [Material Handling](#)
- [Network Instruments](#)
- [Power Tool Accessories](#)
- [Professional Hand Tools](#)
- [Pulling](#)
- [Safety Products](#)
- [Storage](#)
- [Telco Instruments](#)
- [VDV Instruments](#)
- [VDV Termination](#)
- [VDV Tools](#)
- [Wire Termination](#)

[Professional Hand Tools](#) > [Stripping & Cutting](#) > [Strippers](#) > STRIPPER,WIRE (1935)

STRIPPER,WIRE (1935)

[SAVE PRODUCT TO PDF](#)

[Images](#)



Cat No: **1935** UPC No: **783310376002**

[Request Product Info or Demo ▶](#)

[Where to Buy ▶](#)

- [Description](#)
- [Specifications](#)
- [Reviews](#)

- Application : Use With Solid And Stranded Wire
- Capacity : 20 - 10 AWG (0.500 MM2 - 6.000 MM2) With PVC Or THHN Insulation, Up To 7/8 IN (22.200 MM) Length
- Type : Automatic
- Weight : 0.700 LB (0.300 KG)