

**PRODUCTS**

[Hand Tools](#)  
[Holemaking](#)  
[Bending](#)  
[Fishing](#)  
[Cable Pulling](#)  
[Wire & Cable Termination](#)  
[Voice Data Video](#)  
[Testing & Measurement](#)  
[Storage & Material Handling](#)  
[Hydraulic Pumps & Miscellaneous](#)

 Search by Keyword/Cat.No./UPC No.  

Page 1/1

	Name	UPC	Catalog #
	Conduit & Pipe: 3/4", Hole Size: 1.115 Inch, 28.3 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 123AV 04008 , Replacement Die 124AV 06972 , Replacement Draw Stud 249AVBB 04040	22564	72BB
	Conduit & Pipe: , Hole Size: 1.280 Inch, 32.5 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 24459, Replacement Die 35168 , Replacement Draw Stud 249AVBB 04040	24476	24476
	Conduit & Pipe: 1", Hole Size: 1.362 Inch, 34.6 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 125AV 04010 , Replacement Die 126AV 04011 , Replacement Draw Stud 249AVBB 04040	22565	73BB
	Conduit & Pipe: , Hole Size: 1.457 Inch, 37.0 (mm), Capacity Mild Steel: 10 GA, 3.5 mm,, Replacement Punch 18331 18331 , Replacement Die 32008 32008 , Replacement Draw Stud 249AVBB 04040	18890	730EBB-37
	Conduit & Pipe: , Hole Size: 1.595 Inch, 40.5 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 24462, Replacement Die 35159 , Replacement Draw Stud 249AVBB 04040	24477	24477
	Conduit & Pipe: 1-1/4 , Hole Size: 1-11/16 1.701 Inch, 43.2 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 127AV 06974 , Replacement Die 128AV 04013 , Replacement Draw Stud 249AVBB 04040	22566	74BB

Page 1/1