

PRODUCTS

- Hand Tools
- Holemaking
- Bending
- Fishing
- Cable Pulling
- Wire & Cable Termination
- Voice Data Video
- Testing & Measurement
- Storage & Material Handling
- Hydraulic Pumps & Miscellaneous

 Search by Keyword/Cat.No./UPC No.

 |< << >> >| Page 1/2

	Name	UPC	Catalog #
	Replacement Manual Draw Stud 3/4in. x 2-15/16in.	04042	304AVBB
	Draw Stud-3/4in. x 2-15/16in. Replacement for 7360SB/34358 and 7361SB/34359	04042	304AVBB
	3/4" x 2-15/16" Draw Stud	04042	304AVBB
	Conduit & Pipe: , Hole Size: 1.850 Inch, 47.0 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 17687 17687 , Replacement Die 32009 32009 , Replacement Draw Stud 304AVBB 04042	18891	730EBB-47
	Conduit & Pipe: 1-1/2", Hole Size: 1-15/16 1.951 Inch, 49.6 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 439AV 06978 , Replacement Die 440AV 04061 , Replacement Draw Stud 304AVBB 04042	22567	75BB
	Conduit & Pipe: , Hole Size: 2 2.000 Inch, 50.8 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 1756AV 04232 , Replacement Die 35161 35161 , Replacement Draw Stud 304AVBB 04042	20676	730BB-2
	Conduit & Pipe: , Hole Size: 2-1/8 2.125 Inch, 54.0 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 1783AV 04245 , Replacement Die 36173 36173 , Replacement Draw Stud 304AVBB 04042	20678	730BB-2-1/8
	Conduit & Pipe: , Hole Size: 2.362 Inch, 60.0 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 17690 17690 , Replacement Die 32011 32011 , Replacement Draw Stud 304AVBB 04042	18892	730EBB-60
	Conduit & Pipe: 2", Hole Size: 2-3/8 2.416 Inch, 61.5 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 441AV 04062 , Replacement Die 442AV 04063 , Replacement Draw Stud 304AVBB 04042	22568	76BB
	Draw Stud 3/4in. x 2-15/16in. Replacement for Manual Drivers	04042	304AVBB

 |< << >> >| Page 1/2