



Select a Language



SEARCH

Supplier Center | Distributor Center

BROWSE PRODUCTS

Category: -- Select -- | Browse by Brand: --Select--

PRODUCTS

- Bending
- Bolt Cutters
- Cable Termination
- CATV/Broadband Instruments
- Connectors
- Electric Test Instruments
- Fasteners
- Fiber Connections
- Fiber Optic Instruments
- Fishing
- Hydraulic Tools
- Knockout Sets
- Material Handling
- Network Instruments
- Power Tool Accessories
- Professional Hand Tools
- Pulling
- Safety Products
- Storage
- Telco Instruments
- VDV Instruments
- VDV Termination
- VDV Tools
- Wire Termination

VDV Tools > VDV Crimpers > VDV Crimpers Frame Crimpers > CRIMPER 1300 TERM & SPLICES AWG 22-8

CRIMPER 1300 TERM & SPLICES AWG 22-8

Images



SAVE PRODUCT TO PDF

Related Products



Image Unavailable



User Reviews (No Reviews Yet.)

Cat No: PA1322 | UPC No: 769328100235

Request Product Info or Demo | Where to Buy

Description | Specifications | Reviews

- Cable Type : Non-Insulated Terminals And Lugs
- Connection : Solid Or Stranded Wire, 22-8 AWG (0.340 - 0.100 SQ-MM)
- Crimping Range : 10-8/14-12/18-16/22-20 AWG (6.000 - 10.000/2.500 - 4.000/0.750 - 1.500/0.340 - 0.500 SQ-MM)

About Us | Manuals | News & Events | Contact Us | Careers | Submit an Idea | Promotions | Support

CA Transparency in Supply Chains Act | Environmental Responsibility | Privacy Policy | Terms of Use | Textron | Site Map
Rothenberger | Sherman & Reilly | HD Electric | Klauke | Greenlee Communications