

BROWSE PRODUCTS

Category: -- Select --

Brand: -- Select --

PRODUCTS

- Bending
- Bolt Cutters
- Cable Termination
- CATV/Broadband Instruments
- Connectors
- Electric Test Instruments
- Fasteners
- Fiber Connections
- Fiber Optic Instruments
- Fishing
- Holemaking
- Hydraulic Tools
- Material Handling
- Power Tools
- Professional Hand Tools
- Pulling
- Safety Products
- Storage
- Telco Instruments
- VDV Instruments
- VDV Termination
- VDV Tools
- Wire Termination

Cable Termination > CABLE STRIPPERS > Cable Strippers > STRIPPER,KWIK (34-10 AWG).

**STRIPPER,KWIK (34-10 AWG).**

Images



Related Products



User Reviews

☆☆☆☆☆ (No Reviews Yet.)

Cat No: 45000    UPC No: 783310450009

Where to Buy ▶

Description

Specifications

Documents

- 34 - 10 AWG (0.08 - 6 MM2) stripping capacity
- 12 AWG (4 MM2) solid, 10 AWG (6 MM2) stranded capacity
- Strips and cuts flat and round cable
- Self-adjusts to different wire gauges
- Laminated steel blades minimize the risk of nicking conductors
- Front entry jaws have an adjustable strip length guide
- Lightweight reinforced nylon is chemical and corrosion resistant
- Note: This is not an insulated tool

