

CLAMP METER, AC/DC (CM-960) (POP)

Cat #: CM-960 UPC #: 783310021926



CLAMP METER, AC/DC (CM-960) (POP)

Cat #: CM-960 UPC #: 783310021926

SHARE

- Measures AC+DC current
- AC and AC+DC voltage measurements with digital low pass filter for accurate readings on variable frequency drives
- Also measures DC voltage, resistance, capacitance and frequency
- Tests continuity and diodes
- Peak-RMS measures motor inrush current
- Backlight & relative mode for added versatility
- AmpTip™ increases accuracy on small wires and low current
- Two voltage detection modes - non-contact or using a single test lead
- Data hold
- Recording of Maximum, Minimum, and Average readings
- Lifetime warranty

WHERE TO BUY >**SPECIFICATIONS**

Specifications

Amperage Measurement

60, 600 Amps AC+DC

Display

LCD, 6000 Count

Frequency Rating

Voltage and Amp Tip current: 50/60 Hz. High current: 50 to 400 Hz

Includes

(2) 1.5V AAA batteries, test leads, carrying case

Jaw Opening

1.18" (30 mm)

Measurement Category

CAT III 600V, CAT IV 300V

Replacement Part

TSG-3 test leads, TC-10 carrying case

Resistance Measurement

600, 6k, 60k Ohms

Standard

CAT III, C/US UL Listed, CE

True Power

AC+DC True RMS

Voltage Measurement

600 Volts AC+DC

*Greenlee® may make improvements and/or changes in the specifications of products at any time, in its sole discretion, without notice or obligation and further reserves the right to change or discontinue models.