

Home

CHP-170

This cutter is an excellent general use tool.



[Click Picture to Enlarge](#)

[Print this Page](#)

LIVE HELP
[Leave a message](#)
 Available weekdays
 7:30am - 4:30pm PT



[Digital 2015 Catalog](#)

- [Request a Catalog by mail](#)
- [Comments/Suggestions](#)
- [Report Trouble](#)
- [AHPDirect](#)



[View Cart](#)

| Item No. / Description | MSLP | Stock Status |
|---|----------|--------------|
| CHP-170 CUTTER,MICRO,CLEAN CUT,16AWG | US\$4.37 | Please call |

- [Features & Benefits](#)
- [Specifications](#)
- [FAQ](#)

MEDIUM CUTTER

This cutter is an excellent general use tool.

Part Number: CHP-170

- Steel: 2.5 mm
- Cut: Flush
- Max cut: 16 AWG
- Handle: NA
- Rockwell Hardness (RHC): 56

Part Number (with safety clip): **CHP-170-A**

Note: Max cut is determined with copper wire. To order tool with black dissipative handles, add the suffix -D to the part number (ie. CHP-170-D)

Stay Connected

