



Quality Products. Service Excellence.

100-240 VAC / 10A IEC Double Pole Switched Outlet Strip 1581 DP Series



Features

- On-Off switch is rocker type (double pole, single throw) with green light.
- Rated 100-240VAC (TUV), 120-240VAC (UL), 10 A, 50/60 Hz and designed for use with IEC power cords.
- All metal housing – tough extruded aluminum case with black powder-coated steel cover.
- Mounting feet (with keyhole slots) allow temporary work station mounting if desired.

Specifications

- One IEC 320 - C14 inlet, and 4, 5, 6 or 8 IEC 320 - C13 outlets.
- Includes 10A circuit breakers to prevent accidental line overload.
- cULus listed to UL 60950-1 (2nd Edition); Amd1 + Amd2, and CAN/CSA C22.2 No. 60950-1-07 (2nd Edition); Amd1 + Amd2.
- cULus Listed UL 62368-1 (2nd Edition), 2014-12-01, and CAN/CSA C22.2 No. 62368-1-14 (2nd Edition).
- TÜV certified to EN 60950-1:2006/A2:2013-09, and IEC 60950-1 (ed.2); am1;am2
- TÜV-SUD Certified to EN 62368-1:2014/A11:2017, and IEC 62368-1:2014 (2nd Edition)
- TÜV-SUD tested for EMC Compliance to EN 55032:2012 (CISPR 32:2012) & EN 55024:2010 (CISPR 24:2010).
- CE compliant to the European Low Voltage Directive 2014/35/EU.
- CE compliant to the European EMC Directive 2014/30/EU.



Illuminated On/Off Switch Part No.	Overall Dimensions			Outlet Qty	Outlet Type	Inlet Type
	Height	Width	Length			
1581H4DP	2.33	2.13	13.75	4	C13	C14
1581H5DP	2.33	2.13	16.50	5	C13	C14
1581H6DP	2.33	2.13	16.50	6	C13	C14
1581H8DP	2.33	2.13	19.75	8	C13	C14

Replacement Mounting Foot (One Foot)

Part No.	1584MF
----------	--------

Data subject to change without notice

