



Quality Products. Service Excellence.

Rack Mount Basic PDU 1583 Series

15A | Single-Phase 125V | Front and/or Rear Facing 5-15R Outlets

Features



- Designed for power distribution from the front and/or rear of the unit.
- 1U horizontal 19" rackmount installation.
- With lighted on/off switch or red pilot light to indicate power on.
- 6 outlet models include 2 outlets with extra spacing for clearance of most plug in transformers.
- Available in ASA 61 grey or black powder coat finish.
- [Click here for our surge protected version.](#)

Specifications

- Heavy duty 14 gauge wire cord - 14/3 SJT type for extreme temperature ranges and integral molded plug.
- Plug types available are NEMA 5-15P straight blade or NEMA L5-15P locking type.
- Includes 15 Amp, 125 VAC circuit breaker to prevent accidental overload.
- UL/cUL recognized Standard UL1363 file No. E166039 & CSA C22.2 No. 308-14 & CSA C22.2 No. 0.4-04



Gallery



Accessories

- Mounting Hardware
- Rail Depth Adapter Kit

Black Finish

Illuminated On/Off Switch Part No.	Illuminated Light Only Part No.	Overall Dimensions			Number of Outlets		Outlet		Cord Length	Plug Blade Type	NEMA Plug Type	Rack Units
		Height	Width	Depth	Front	Rear	NEMA Type	Rotated Outlets				
1583H12A1BKX	1583T12A1BKX	1.72	19.00	2.66	6	6	5-15R	No	6 ft	Straight	5-15P	1U
1583H12B1BKX	1583T12B1BKX	1.72	19.00	2.66	6	6	5-15R	No	15 ft	Straight	5-15P	1U
1583H12C1BKX	1583T12C1BKX	1.72	19.00	2.66	6	6	5-15R	No	6 ft	Locking	L5-15P	1U
1583H12D1BKX	1583T12D1BKX	1.72	19.00	2.66	6	6	5-15R	No	15 ft	Locking	L5-15P	1U
1583H6A1BK	1583T6A1BK	1.72	19.00	2.66	0	6	5-15R	No	6 ft	Straight	5-15P	1U
1583H6A1BKRA	1583T6A1BKRA	1.72	19.00	2.66	0	6	5-15R	Yes	6 ft	Straight	5-15P	1U
1583H6A1BKX	1583T6A1BKX	1.72	19.00	2.66	2	4	5-15R	No	6 ft	Straight	5-15P	1U

Illuminated On/Off Switch Part No.	Illuminated Light Only Part No.	Overall Dimensions			Number of Outlets		Outlet	Rotated Outlets	Cord Length	Plug Blade Type	NEMA Plug Type	Rack Units
		Height	Width	Depth	Front	Rear	NEMA Type					
1583H6B1BK	1583T6B1BK	1.72	19.00	2.66	0	6	5-15R	No	15 ft	Straight	5-15P	1U
1583H6B1BKRA	1583T6B1BKRA	1.72	19.00	2.66	0	6	5-15R	Yes	15 ft	Straight	5-15P	1U
1583H6B1BKX	1583T6B1BKX	1.72	19.00	2.66	2	4	5-15R	No	15 ft	Straight	5-15P	1U
1583H6C1BK	1583T6C1BK	1.72	19.00	2.66	0	6	5-15R	No	6 ft	Locking	L5-15P	1U
1583H6C1BKRA	1583T6C1BKRA	1.72	19.00	2.66	0	6	5-15R	Yes	6 ft	Locking	L5-15P	1U
1583H6C1BKX	1583T6C1BKX	1.72	19.00	2.66	2	4	5-15R	No	6 ft	Locking	L5-15P	1U
1583H6D1BK	1583T6D1BK	1.72	19.00	2.66	0	6	5-15R	No	15 ft	Locking	L5-15P	1U
1583H6D1BKRA	1583T6D1BKRA	1.72	19.00	2.66	0	6	5-15R	Yes	15 ft	Locking	L5-15P	1U
1583H6D1BKX	1583T6D1BKX	1.72	19.00	2.66	2	4	5-15R	No	15 ft	Locking	L5-15P	1U
1583H8A1BK	1583T8A1BK	1.72	19.00	2.66	0	8	5-15R	No	6 ft	Straight	5-15P	1U
1583H8B1BK	1583T8B1BK	1.72	19.00	2.66	0	8	5-15R	No	15 ft	Straight	5-15P	1U
1583H8C1BK	1583T8C1BK	1.72	19.00	2.66	0	8	5-15R	No	6 ft	Locking	L5-15P	1U
1583H8D1BK	1583T8D1BK	1.72	19.00	2.66	0	8	5-15R	No	15 ft	Locking	L5-15P	1U

ASA 61 Grey Finish

Illuminated On/Off Switch Part No.	Illuminated Light Only Part No.	Overall Dimensions			Number of Outlets		Outlet	Rotated Outlets	Cord Length	Plug Blade Type	NEMA Plug Type	Rack Units
		Height	Width	Depth	Front	Rear	NEMA Type					
1583H6A1	1583T6A1	1.72	19.00	2.66	0	6	5-15R	No	6 ft	Straight	5-15P	1U
1583H6B1	1583T6B1	1.72	19.00	2.66	0	6	5-15R	No	15 ft	Straight	5-15P	1U
1583H6C1	1583T6C1	1.72	19.00	2.66	0	6	5-15R	No	6 ft	Locking	L5-15P	1U
1583H6D1	1583T6D1	1.72	19.00	2.66	0	6	5-15R	No	15 ft	Locking	L5-15P	1U
1583H8A1	1583T8A1	1.72	19.00	2.66	0	8	5-15R	No	6 ft	Straight	5-15P	1U
1583H8B1	1583T8B1	1.72	19.00	2.66	0	8	5-15R	No	15 ft	Straight	5-15P	1U
1583H8C1	1583T8C1	1.72	19.00	2.66	0	8	5-15R	No	6 ft	Locking	L5-15P	1U
1583H8D1	1583T8D1	1.72	19.00	2.66	0	8	5-15R	No	15 ft	Locking	L5-15P	1U

Data subject to change without notice

© 2020. Hammond Manufacturing Ltd. All rights reserved.