

Caster Set 1425B Series

Features

- Feature ball bearing, swivel and hard composition wheels.



1425B Compatibility

- [C2](#)
- [C4](#)
- [DNRRDCK](#)
- [DNRRLDK](#)
- [DNRRLDW](#)

1425BM Compatibility

- [C2](#)
- [C4](#)
- [DNRRDCK](#)
- [DNRRLDK](#)
- [DNRRLDW](#)



1425BH Compatibility

- [C2](#)
- [C4](#)
- [DNRRDCK](#)
- [DNRRLDK](#)
- [DNRRLDW](#)
- [RCSC](#)

| Part No. | Strength | Wheel Diameter | Overall Height | | Hole Mounting Pattern | | Caster Set Weight Capacity | Qty Included In Set | Qty with Brakes Included | Physical Wheel Weight |
|-------------------|-------------|----------------|------------------|-------|-----------------------|------|----------------------------|---------------------|--------------------------|-----------------------|
| | | | Added to Cabinet | Width | Depth | | | | | |
| 1425B | Lite Duty | 3.00 | 4.38 | 1.75 | 3.00 | 360 | 4 | 0 | 5 lb (2.3 kg) | |
| 1425BM | Medium Duty | 3.00 | 3.81 | 1.75 | 3.00 | 700 | 4 | 0 | 5.3 lb (2.4 kg) | |
| 1425BH | Heavy Duty | 3.00 | 3.81 | 1.75 | 3.00 | 1050 | 4 | 0 | 6 lb (2.7 kg) | |
| 1425BHLOCK | Heavy Duty | 3.00 | 3.81 | 1.75 | 3.00 | 1050 | 4 | 4 | 6 lb (2.7 kg) | |

Data subject to change without notice

