



Quality Products. Service Excellence.

Aluminum Rack Panels *PBPA Series*

Features:

- Constructed of 8-gauge (0.125") 5052-H32 Aluminum.
- Fits standard EIA-310-D compliant rails.
- Install in unused rack space to improve both cooling efficiency and prevent air re-circulation.
- Finished in smooth powder paint or unfinished.
- RoHS Compliant.
- Manufactured in North America.



Accessories

- Mounting Hardware



Part No.	Part No.	Part No.	Part No.	Part No.	Mounting Dimensions		Number of
Gloss Black	Matte Black	ASA 61 Gray	Light Gray	Unfinished	Rack Units	Height	Mounting Slots
PBPA19001BK2	PBPA19001BK	PBPA19001GY2	PBPA19001LG2	PBPA19001UNF	1U	1.75	4
PBPA19003BK2	PBPA19003BK	PBPA19003GY2	PBPA19003LG2	PBPA19003UNF	2U	3.50	4
PBPA19005BK2	PBPA19005BK	PBPA19005GY2	PBPA19005LG2	PBPA19005UNF	3U	5.25	4
PBPA19007BK2	PBPA19007BK	PBPA19007GY2	PBPA19007LG2	PBPA19007UNF	4U	7.00	4
PBPA19008BK2	-	PBPA19008GY2	PBPA19008LG2	PBPA19008UNF	5U	8.75	4
PBPA19010BK2	-	PBPA19010GY2	PBPA19010LG2	PBPA19010UNF	6U	10.50	8
PBPA19012BK2	-	PBPA19012GY2	PBPA19012LG2	PBPA19012UNF	7U	12.25	8
PBPA19014BK2	-	PBPA19014GY2	PBPA19014LG2	PBPA19014UNF	8U	14.00	8
PBPA19015BK2	-	PBPA19015GY2	PBPA19015LG2	PBPA19015UNF	9U	15.75	8
PBPA19017BK2	-	PBPA19017GY2	PBPA19017LG2	PBPA19017UNF	10U	17.50	8
PBPA19019BK2	-	PBPA19019GY2	PBPA19019LG2	PBPA19019UNF	11U	19.25	8
PBPA19021BK2	-	PBPA19021GY2	PBPA19021LG2	PBPA19021UNF	12U	21.00	8
PBPA19022BK2	-	PBPA19022GY2	PBPA19022LG2	PBPA19022UNF	13U	22.75	8
PBPA19024BK2	-	PBPA19024GY2	PBPA19024LG2	PBPA19024UNF	14U	24.50	10
PBPA19026BK2	-	PBPA19026GY2	PBPA19026LG2	PBPA19026UNF	15U	26.25	10
PBPA19028BK2	-	PBPA19028GY2	PBPA19028LG2	PBPA19028UNF	16U	28.00	12
PBPA19029BK2	-	PBPA19029GY2	PBPA19029LG2	PBPA19029UNF	17U	29.75	12
PBPA19031BK2	-	PBPA19031GY2	PBPA19031LG2	PBPA19031UNF	18U	31.50	12

Data subject to change without notice

