



"T" Soft Side Enclosure - Hand Held
(1553T Series)
Flame Retardant ABS Plastic



- Home
- Products
- Distributors
- Technical
- Contact Us
- Other Options

Path: [Home](#) > [Enclosure Index](#) > "T" Soft Side Enclosure - Flame Retardant ABS

No Battery Door Version



click to enlarge



click to enlarge

Battery Door Version



click to enlarge

Key Features:




- Ergonomically designed for a comfortable fit into the user's hand.
- Perfect for instrument or mobile data enclosures requiring a keypad and display.
- Both the display and keyboard areas are recessed for membrane devices.
- Molded from **flame retardant ABS plastic**, choice of black (RAL 9011) or grey (RAL 7035) - material carries a UL flammability rating of 94V-0.
- Handheld section of enclosure includes a dark grey (RAL 7012) overmold, soft plastic grip.
- Enclosure is assembled with M3-0.5 x 18 mm Philips machine screws, threaded into integral brass bushings. Perfect for applications when repetitive assembly and disassembly are required.
- Integral brass bushings are factory inserted into top half of the enclosure (see photos).
- Lap joint construction provides protection against access of dust and splashing water. Designed to meet IP54.
- P.C. board standoffs are molded into case top & bottom halves (see drawings or photos for more details).
- Battery door & compartment version (part numbers ending in "BAT") includes 8 battery clips (for 4 - AA batteries) and two 9 volt (PP3) battery clips.
- Contains either one or two end panels (depending on version - see table below) - removable for easy modification.
- Bottom half of enclosure includes molded in label recess on back (2.2" x 1.65" / 56 mm x 42 mm).

Flame Retardant ABS Plastic

Part Number	Color	PDF Reader File	AutoCAD .dwg Files (zipped)	3D Solid Model .stp & .igs files (zipped)	Battery Door & Compartment	Removable Top End Panel	Removable Bottom End Panel	Overall Enclosure Dimensions				
								Units	Display Section Width	Keyboard Section Width	Length	Enclosure Depth
1553TBK 1553TGY	Black Grey	NEW	NEW	NEW	No	Yes	Yes	Inches	3.94	3.38	8.27	1.26
								mm	100	85.9	210	32
1553TBKBAT 1553TGYBAT	Black Grey	NEW	NEW	NEW	Yes	Yes	No	Inches	3.94	3.38	8.27	1.26
								mm	100	85.9	210	32

 [Link here to photo tables](#) of each part number

Features (by photo):

<p>Battery Door & Compartment Versions (Part numbers ending in "BAT")</p>	
<p>Includes our long life 3 point battery door. Compartment takes either four (4) AA batteries or two (2) 9V (PP3) batteries</p>	
 <p>click to enlarge</p>	
<p>Battery compartment (includes 8 clips) for four AA batteries.</p>	<p>Battery compartment (includes 2 clips) for 9V (PP3) batteries.</p>
 <p>click to enlarge</p>	 <p>click to enlarge</p>

Accessories

Part Number	Thumbnail Photo	Color	Package Quantity	Description
SC503-100		Silver	100	Replacement Cover Screws (M3-0.5 x 18mm Flat Head)
SC503BK-100		Black	100	Replacement Cover Screws (M3-0.5 x 18mm Flat Head)
1593ATS50		Silver	50	Optional P.C. Board Screws (#4 x 1/4" Self Tapping)
1593ATS100		Silver	100	Optional P.C. Board Screws (#4 x 1/4" Self Tapping)

Exactly what you are looking for???

[Link to our stocking distributors - most have "on-line" pricing, stock check and ordering!!!](#)

[Our Distributors](#)

[Order from your favorite distributor](#)

[Home](#) | [Products](#) | [Distributors](#) | [Technical](#) | [Contact Us](#) | [Other Options](#)

Copyright; © 2012 Hammond Mfg Co Inc

URL: <http://www.hammondmfg.com>