




Universal Rack Shelf *RAS Series*

[Home](#) / [Racks & Rack Cabinets](#) / [Accessories](#) / [Shelves](#)
[English](#) | [Français](#)


Features

- Constructed of 14 or 16 gauge steel.
- Universal design mounts to any standard EIA compliant rack or cabinet.
- Allows easy rack mounting of equipment or items that do not have rack mounting capabilities.
- Mounts to rack rails either as an internal shelf or external shelf/work area
- Available in either vented or solid versions
- Tested up to nearly double the suggested load rating of 200 lbs.
- Rugged textured black powder paint finish.
- RoHS and REACH compliant.
- Manufactured in North America.

PRODUCT RESOURCES

-  [Specification Sheet](#)
-  [Print Page](#)
-  [Contact Us](#)

SHARE THIS PRODUCT



[+ Zoom]



Accessories


[Mounting Hardware](#)

[Hook and Loop Roll](#)

19 Inch Mounting Shelves

Click part number for details (e.g., CAD files, assembly instructions)

 Units shown: **inch**. Switch units to: [mm](#)

Part No. Vented	Part No. Solid (Un-Vented)	Mounting Dimensions				Stiffener Lip(s) Folded	Suggested Load Capacity
		Rack Units	Height	Width	Depth		
RASV190107UBK1	RASU190107UBK1	1U	1.75	19.00	7.00	Up (Front & Back)	40
RASV190107DBK1	RASU190107DBK1	1U	1.75	19.00	7.00	Down (Front & Back)	40
RASV190110BK1	RASU190110BK1	1U	1.75	19.00	10.00	Up (Back Only)	40
★ RASV190112BK1	★ RASU190112BK1	1U	1.75	19.00	12.00	Up (Back Only)	40
RASV190115BK1	RASU190115BK1	1U	1.75	19.00	15.00	Up (Back Only)	40
RASV190120BK1	RASU190120BK1	1U	1.75	19.00	20.00	Up (Back Only)	40
RASVL190314BK1	RASUL190314BK1	2U	3.50	19.00	14.50	Up (Back Only)	100
★ RASV190312BK1	★ RASU190312BK1	2U	3.50	19.00	12.00	Up (Back Only)	100
RASV190315BK1	RASU190315BK1	2U	3.50	19.00	15.00	Up (Back Only)	100
RASV190318BK1	RASU190318BK1	2U	3.50	19.00	18.00	Up (Back Only)	100
RASV190320BK1	RASU190320BK1	2U	3.50	19.00	20.00	Up (Back Only)	100
RASVL190514BK1	RASUL190514BK1	3U	5.25	19.00	14.50	Up (Back Only)	80
RASV190515BK1	RASU190515BK1	3U	5.25	19.00	15.00	Up (Back Only)	200
RASV190520BK1	RASU190520BK1	3U	5.25	19.00	20.00	Up (Back Only)	200
RASV190715BK1	RASU190715BK1	4U	7.00	19.00	15.00	Up (Back Only)	200
RASV190720BK1	RASU190720BK1	4U	7.00	19.00	20.00	Up (Back Only)	200

Tested to nearly double the suggested load rating.

23 Inch Mounting Shelves

Click part number for details (e.g., CAD files, assembly instructions)

 Units shown: **inch**. Switch units to: [mm](#)

Part No. Vented	Part No. Solid	Mounting Dimensions			Rack Units	Stiffener Lip(s) Folded	Suggested Load Capacity
		Height	Width	Depth			
RASV230515BK1	RASU230515BK1	5.25	23.00	15.00	3U	Up (Back Only)	200
RASV230520BK1	RASU230520BK1	5.25	23.00	20.00	3U	Up (Back Only)	200

Tested to nearly double the suggested load rating.

24 Inch Mounting Shelves

Click part number for details (e.g., CAD files, assembly instructions)

 Units shown: **inch**. Switch units to: [mm](#)

Part No. Vented	Part No. Solid	Mounting Dimensions			Rack Units	Stiffener Lip(s) Folded	Suggested Load Capacity
		Height	Width	Depth			
RASV240515BK1	RASU240515BK1	5.25	24.00	15.00	3U	Up (Back Only)	200
RASV240520BK1	RASU240520BK1	5.25	24.00	20.00	3U	Up (Back Only)	200

[Need Assistance? Contact Us.](#)

Data subject to change without notice.

**Have a Question?
Contact Us**