



*Quality Products. Service Excellence.*

## 10-32 Tapped Universal Rack Rail *URR Series*



### Features:

- Constructed in 12-gauge steel.
- Sold in pairs.
- EIA/TIA compliant drilled and tapped 10-32 holes.  
Rack **Mounting hardware** sold separately.
- Rails come included with rack unit indicator.
- Rails can be used for 19", 23" and 24" rack mounting applications.
- Side of rail folded for rear support or accessory mounting.
- Finished in smooth black powder paint.

### Accessories

- 10-32 Mounting Hardware



Part No.	Mounting Dimensions	
	Rack Units	Height
URR2U	2U	3.50
URR3U	3U	5.25
URR4U	4U	7.00
URR6U	6U	10.50
URR8U	8U	14.00
URR10U	10U	17.50
URR12U	12U	21.00
URR14U	14U	24.50
URR16U	16U	28.00
URR18U	18U	31.50
URR21U	21U	36.75
URR24U	24U	42.00
URR27U	27U	47.25
URR36U	36U	63.00
URR45U	45U	78.75

Tags: Rackrail, Mounting Rails, Thin Flange Rails, Rack Rails

*Data subject to change without notice*

© 2020. Hammond Manufacturing Ltd. All rights reserved.