



POLYPRO™, Type 4X

Catalog Number:A14128PHCW
[Back To Product](#)

Bulletin Number: PCR **Material:** Polyester
RoHS Flag: No **Model Code:** 17091
Ship Wt. Std. Pkg. (lbs): 8.6 **Interchangeable:** False

IP Rating: IP66

Products per Package:
 1.0

Industry Standards:
Mounting brackets required to meet UL/CSA external mounting requirements.

UL 508A Listed; Type 4, 4X, 12, 13; File No. E61997 cUL Listed per CSA C22.2 No 94; Type 4, 4X, 12, 13; File No. E61997 Enclosure flammability evaluated per UL 508A Window flammability evaluated per UL 508A

NEMA/VEEMAC Type 4, 4X, 12, 13
 CSA File No. 42186; Type 4, 4X, 12, 13 (solid covers only)
 IEC 60529, IP66

Products per Package:
 1.0

Change Item >

CHANGING AN ITEM WILL UPDATE THE CATALOG NUMBER. THIS CAN AFFECT THE LIST PRICE AND SPECIFICATION OF THE ITEM.

Quantity

Modify Product >

Add Item to Project List +

Description Downloads **Items** Accessories

POLYPRO™, Type 4X

Catalog Number	A14128PHCW
Height (A) mm	356.0
Width (B) mm	305.0
Depth (C) mm	212.0
L mm	407
F mm	210
G mm	388
H mm	268
Panel Size D x E mm.	324 x 276
J mm	201
M mm	311
N mm	260
W mm	338
Aluminum Panel	A14P12AL
Steel Panel	A14P12
Cover Type	Window

<p>EXPLORE</p> <ul style="list-style-type: none"> About Us Services & Capabilities News and Events Strategic Partnerships Investor Relations 	<p>CONTACT</p> <ul style="list-style-type: none"> Customer Service Find a Sales Office or Distributor Global Locations Product Compliance & Certifications Partner Login 	<p>DOWNLOAD</p> <ul style="list-style-type: none"> Literature White Papers & Case Studies Videos & Mobile Apps Product Configurators Warranties
--	--	---