

Marine Products

15 Ampere, 125 Volt

2 Pole 3 Wire

TWIST-LOCK® Locking Type Devices



HBL47CM00



HBL52CM21
HBL5221



HBL47CM20C



HBL60CM23



HBL47CM29C



HBL60CM24



HBL47CM15



HBL47CM16



15A 125V Twist-Lock Devices

Description	Catalog Numbers
Yellow duplex receptacle has heat resistant body.	HBL47CM00
Yellow Valox® spring-loaded lift cover plate for weatherproofing duplex receptacles. Stainless steel screws and neoprene gasket included for mounting to FS/FD type weatherproof boxes. IP20 SUITABILITY.	HBL52CM21
Same as #HBL52CM21 except gray in color. IP20 SUITABILITY.	HBL5221
Same as #HBL52CM21 except for mounting to standard boxes. IP20 SUITABILITY. Not CSA.	HBL52CM22*
Same as #HBL52CM22 except gray in color. IP20 SUITABILITY. Not CSA.	HBL5222*
Yellow Insulgrip® plug has rugged nylon housing and detachable cord grip with range of .296"-.687" (7.5-17.4) that utilizes a unique offset jaws arrangement to provide secure strain relief.	HBL47CM20C
Short yellow Seal-Tite® cover for weatherproofing #HBL47CM20C Insulgrip® plug when used with receptacles or connector bodies. Also can be used to weatherproof #HBL47CM29C Insulgrip® connector body when used with #HBL47CM16 flanged inlet. IP55 SUITABILITY. Not CSA.	HBL60CM23
Yellow Insulgrip® connector body has rugged nylon housing and detachable cord grip with range of .296"-.687" (7.5-17.4) that utilizes a unique offset jaws arrangement to provide secure strain relief.	HBL47CM29C
Yellow Seal-Tite® cover for weatherproofing #HBL47CM29C Insulgrip® connector body when used on extension cords and adapters. IP20 SUITABILITY. Not CSA.	HBL60CM24
Panel mount flanged outlet has heat resistant melamine interior and stainless steel casing.	HBL47CM15
Panel mount flanged inlet has heat resistant melamine interior and stainless steel casing.	HBL47CM16
Three conductor, #14 AWG type STW, yellow PVC jacketed portable cord has jute fillers for added flexibility and is ideal for making cable sets, extension cords and adapters as it will not mark the boat's deck. Available in 250' (76.2m) lengths only.	YC314250*

*Not shown.

© Valox is a registered trademark of General Electric Company.



Wiring Device-Kellems

www.hubbell-marine.com

Marine Products

15 Ampere, 125 Volt

2 Pole 3 Wire

Straight Blade Devices



IP20
SUITABILITY Plugs and connectors only.



15A 125V

15A 125V Straight Blade Devices

Description	Catalog Numbers
Yellow single receptacle features Rynite® body and abuse resistant nylon face.	HBL52CM61
Yellow corrosion resistant duplex receptacle. Use where salt or other corrosive elements are a problem.	HBL52CM62
Same as #HBL52CM62 except ivory.	HBL52CM62I*
Yellow Insulgrip® plug has rugged nylon housing and detachable cord grip with range of .230"-.720" (5.8-18.3) that utilizes a unique offset jaws arrangement for secure strain relief.	HBL52CM66C
Yellow Seal-Tite® cover for weatherproofing straight blade Insulgrip plugs, #HBL52CM66C and #HBL53CM66C, when used with receptacles and connector bodies. Can also be used to weatherproof Insulgrip connector bodies when mating with flanged inlets. IP55 SUITABILITY. Not CSA. <i>Note: For Insulgrip® devices only.</i>	HBL60CM17*
Yellow Insulgrip® connector body has rugged nylon housing and detachable cord grip with range of .230" to .720" (5.8-18.3) that utilizes a unique offset jaws arrangement for secure strain relief.	HBL52CM69C
Yellow Seal-Tite® cover for weatherproofing straight blade Insulgrip connector bodies, #HBL52CM69C and #HBL53CM69C, on extension cords and adapters. IP55 SUITABILITY. Not CSA. <i>Note: For Insulgrip® devices only.</i>	HBL60CM18*
Yellow Valise® plug has one-piece nylon housing that assembles easily with two screws. Built-in cord grip has range of .220"-.660" (5.6-16.8).	HBL52CM66V
Yellow Valise® connector body has one-piece nylon housing that assembles easily with two screws. Built-in cord grip has range of .220"-.660" (5.6-16.8).	HBL52CM69V
Yellow Insulgrip® plug with anchor locking screw to prevent accidental pull-out. The plug is "locked" into the receptacle when the screw is turned down so the head is flush with the plug surface. The cord grip range is .296"-.687" (7.5-17.4). UL recognized component.	HBL52CM80C
Compact gray nylon panel mount inlet ideal for bass boat battery charging connection. Has gasketed spring-loaded lift cover for weatherproofing front and neoprene boot for weatherproofing rear. Will accept both 15A 125V and 20A 125V 2 pole, 3 wire straight blade connector bodies.	HBL61CM64
Same as #HBL61CM64 except black in color.	HBL61CM64BK*
Yellow Valox® spring-loaded lift cover plate for weatherproofing duplex receptacles. Stainless steel screws and neoprene gasket included for mounting to FS/FD type weatherproof boxes. IP20 SUITABILITY.	HBL52CM21*
Same as #HBL52CM21 except gray in color. IP20 SUITABILITY.	HBL5221*
Same as #HBL52CM21 except for mounting to standard boxes. IP20 SUITABILITY.	HBL52CM22*
Same as #HBL52CM22 except gray in color. IP20 SUITABILITY.	HBL5222*
Yellow Valox® spring-loaded lift cover plate for weatherproofing single straight blade receptacles. Stainless steel screws and neoprene gasket included. For mounting to FS/FD type weatherproof boxes. IP44 SUITABILITY.	HBL74CM23WO
Same as #HBL74CM23WO except gray in color. IP44 SUITABILITY.	HBL7423WO*

*Not shown.

®Rynite is a registered trademark of E. I. DuPont.

®Valox is a registered trademark of General Electric Company.



HBL52CM61

HBL52CM62



HBL52CM66C



HBL52CM69C



HBL52CM66V



HBL52CM69V



HBL52CM80C



HBL61CM64



HBL74CM23WO

