



HBL1447 -- Elastogrip Series Plug




2P3W, 15A 125V, 5-15P, Yellow Elastomer, Dust Tight

Product Specifications

Product Type	 <p>Plugs</p>
Body Style	Straight
Standard	NEMA
Amperage	15A
Voltage	125V
Poles and Wires	2 Pole, 3 Wire Grounding
Hospital Grade ?	No
Plug/Connector Grade	Elastogrip
Enhancement	Dust Tight
Color	 <p>Yellow</p>
NEMA No.	5-15P

Horsepower	0.5
Cord Dia.	.300"-.655" (7.6-16.6)
Description	Straight Blade Plug
Type	2 Pole, 3 Wire, Grounding
Rating	15A,125V
Certification	UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280
IP Suitability	IP20
Housing Material	PVC-Yellow
Blade Holder Material	Nylon-Natural
Retainer Material	Polycarbonate-Clear
Cord Clamp Material	Nylon-Yellow
Contact Blades Material	.060" (1.5) Brass
Ground Contact Blade Material	.040" (1.0) Copper Alloy
Terminal Screw Material	#8-32 Brass /Ni plated for neutral
Ground Screw Material	#8-32 Brass, Multiple Drive (Green)
Wire Clamps Material	.062" (1.8) Steel-nickel finish
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%..
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only.
Product Identification	Ratings are a permanent part of the device.
Flammability	UL 94 HB or better.
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).
M Drawings	Click here for M-Drawing
Catalog Page	Click here for catalog page A18
Brochures	Click here for product brochure
Hubbellnet	Click here for Hubbellnet
Catalog Section	Click here for Section-A

UPC Number	78358501301
Weight in LBs	0.15



Hubbell Incorporated (Delaware)
185 Plains Road
Milford, CT 06460-2420
Ph: (203) 882-4800
Fax: (800) 255-1031

