

Straight Blade Devices  
**15 and 20 Ampere, 125 Volts**  
 2 Pole, 3 Wire Grounding  
**Commercial Specification Grade Duplex Receptacles**





**15A 125V**  
 NEMA 5-15R  
 UL CSA  
 0.5 HP



**20A 125V**  
 NEMA 5-20R  
 UL Listed  
 1 HP

## Receptacles

### Commercial, Specification Grade, Duplex, Side and Back Wired

Description	Color	Catalog Numbers	
Side and back wired, commercial.	Almond	<b>BR15AL</b>	<b>BR20AL</b>
	Black	<b>BR15BLK</b>	<b>BR20BLK</b>
	Brown	<b>BR15</b>	<b>BR20</b>
	Gray	<b>BR15GRY</b>	<b>BR20GRY</b>
	Ivory	<b>BR15I</b>	<b>BR20I</b>
	Light Almond	<b>BR15LA</b>	<b>BR20LA</b>
	Office White	<b>BR15OW</b>	<b>BR20OW</b>
	White	<b>BR15WHI</b>	<b>BR20WHI</b>
 Tamper Resistant.*	Almond	<b>BR15ALTR</b>	<b>BR20ALTR</b>
	Black	<b>BR15BLKTR</b>	<b>BR20BLKTR</b>
	Brown	<b>BR15TR</b>	<b>BR20TR</b>
	Gray	<b>BR15GRYTR</b>	<b>BR20GRYTR</b>
	Ivory	<b>BR15ITR</b>	<b>BR20ITR</b>
	Light Almond	<b>BR15LATR</b>	<b>BR20LATR</b>
	White	<b>BR15WHITR</b>	<b>BR20WHITR</b>
	 Weather Resistant.	Almond	<b>BR15ALWR</b>
Black		<b>BR15BLKWR</b>	<b>BR20BLKWR</b>
Brown		<b>BR15WR</b>	<b>BR20WR</b>
Gray		<b>BR15GRYWR</b>	<b>BR20GRYWR</b>
Ivory		<b>BR15IWR</b>	<b>BR20IWR</b>
Light Almond		<b>BR15LAWR</b>	<b>BR20LAWR</b>
White		<b>BR15WHIWR</b>	<b>BR20WHIWR</b>
Weather and Tamper Resistant.*		Almond	<b>BR15ALWRTR</b>
	Black	<b>BR15BLKWRTR</b>	<b>BR20BLKWRTR</b>
	Brown	<b>BR15WRTR</b>	<b>BR20WRTR</b>
	Gray	<b>BR15GRYWRTR</b>	<b>BR20GRYWRTR</b>
	Ivory	<b>BR15IWRTR</b>	<b>BR20IWRTR</b>
	Light Almond	<b>BR15LAWRTR</b>	<b>BR20LAWRTR</b>
	White	<b>BR15WHIWRTR</b>	<b>BR20WHIWRTR</b>

Notes: See page A-44 for accessories.

See Section K for wallplates.

See page A-15 for NEC® Tamper and Weather Resistant Code Requirements.

See page A-55 for technical information.

\*Tamper-resistant devices are not Fed. Spec. Listed.

