

Straight Blade Devices
15 and 20 Ampere, 125 Volts
 2 Pole, 3 Wire Grounding
Commercial Specification Grade Duplex Receptacles




15A 125V
 NEMA 5-15R
 UL CSA
 0.5 HP



20A 125V
 NEMA 5-20R
 UL Listed
 1 HP

Receptacles

Commercial, Specification Grade, Duplex, Side Wired Only

Description	Color	Catalog Numbers	
Smooth nylon face.	Almond	CR15AL	CR20AL
	Black	CR15BLK	CR20BLK
	Brown	CR15	CR20
	Gray	CR15GRY	CR20GRY
	Ivory	CR15I	CR20I
	Light Almond	CR15LA	CR20LA
	Office White	CR15OW	CR20OW
	White	CR15WHI	CR20WHI
 Tamper resistant.*	Almond	CR15ALTR	CR20ALTR
	Black	CR15BLKTR	CR20BLKTR
	Brown	CR15TR	CR20TR
	Gray	CR15GRYTR	CR20GRYTR
	Ivory	CR15ITR	CR20ITR
	Light Almond	CR15LATR	CR20LATR
	White	CR15WHITR	CR20WHITR
	Finder groove.	Almond	CRF15AL
Black		CRF15BLK	CRF20BLK
Brown		CRF15	CRF20
Gray		CRF15GRY	CRF20GRY
Ivory		CRF15I	CRF20I
Light Almond		CRF15LA	CRF20LA
Office White		CRF15OW	CRF20OW
White		CRF15WHI	CRF20WHI

Notes: See page A-44 for accessories.
 See Section K for wallplates.
 See page A-15 for NEC® Tamper and Weather Resistant Code Requirements.
 See page A-55 for technical information.
 *Tamper-Resistant devices are not Fed. Spec. Listed.

