

Straight Blade Devices
15 and 20 Ampere, 125 Volts
 2 Pole, 3 Wire Grounding
Insulgrip® , Elastogrip® and Valise® Connector Bodies



IP20
SUITABILITY



15A 125V
NEMA 5-15R
UL CSA
0.5 HP



20A 125V
NEMA 5-20R
UL CSA
1 HP

Connector Bodies

Insulgrip®

| Description | Cord Diameter | Catalog Numbers | |
|-------------------------------------|---------------------------|-------------------|-------------------|
| Black and white nylon. | .230"-.720" (5.8-18.3) | HBL5269C | HBL5369C |
| Black nylon extra large cord clamp. | .360"-.720" (9.1-18.3) | HBL5269EBK | HBL5369EBK |
| Corrosion resistant yellow nylon. | .230"-.720" (5.8-18.3) | HBL52CM69C | HBL53CM69C |

Notes: See page A-45 for accessories.



IP20 and IP55

SUITABILITY

Elastogrip®

| Description | Cord Diameter | Catalog Numbers | |
|-------------------------------|---------------------------|------------------|------------------|
| Yellow elastomer, dust tight. | .300"-.655" (7.6-16.6) | HBL1547 | HBL1533 |
| Yellow elastomer, watertight. | .300"-.655" (7.6-16.6) | HBL15W47* | HBL15W33* |

IP20

SUITABILITY

Valise®

| Description | Cord Diameter | Catalog Numbers | |
|--|---------------------------|--------------------|-------------------|
| Yellow nylon. | .220"-.660" (5.6-16.8) | HBL5969VY | HBL5369VY |
| Black nylon. | .220"-.660" (5.6-16.8) | HBL5969VBLK | HBL5369VBK |
| Gray nylon. | .220"-.660" (5.6-16.8) | HBL5969VGY | - |
| Orange nylon, sold in bulk pack of 50. | .220"-.660" (5.6-16.8) | HBL515CVO | - |
| Insulation displacement terminals, black nylon. | .230"-.360" (5.8-9.1) | HBL5963VBK | - |
| Insulation displacement terminals, yellow nylon. | .230"-.360" (5.8-9.1) | HBL5963VY | - |

Notes: Connector bodies are not HP rated.

*Watertight connectors IP55 suitability when closure plug inserted or when installed and used properly with mating Elastogrip watertight plug.
 See page A-45 for accessories.

