

Twist-Lock® Devices

30 Ampere, 125, 250 Volts and 277 Volts AC

2 Pole, 3 Wire Grounding

Insulgrip® Plugs and Flanged Inlets



Plugs

Watertight Safety-Shroud® IP66 SUITABILITY

| Description | Cord Dia. | Catalog Numbers | | |
|--|--------------------|------------------|------------------|---|
| Black Valox® housing, white Valox® clamps. | .325"-.930" (9-24) | HBL2611SW | HBL2621SW | - |

Safety-Shroud IP20 SUITABILITY

| Description | Cord Dia. | Catalog Numbers | | |
|---|--------------------|-----------------|-----------------|---|
| Black and white nylon body, white Valox® shroud. Can be used with the Insulgrip Connector Bodies. | .360"-.930" (9-24) | HBL2611S | HBL2621S | - |

Accessories on page B-40.

Insulgrip IP20 SUITABILITY

| Description | Cord Dia. | Catalog Numbers | | |
|---|--------------------|------------------|------------------|----------------|
| Black and white nylon. | .360"-.930" (9-24) | HBL2611 | HBL2621 | HBL2631 |
| Heat stabilized, gray nylon, 220° F (104° C). | .360"-.930" (9-24) | HBL2611F | HBL2621F | - |
| Corrosion resistant, yellow nylon. | .360"-.930" (9-24) | HBL26CM11 | HBL26CM21 | - |
| All black nylon. | .360"-.930" (9-24) | HBL2611BK | HBL2621BK | - |

Accessories on page B-51.

Valise® IP20 SUITABILITY

| Description | Cord Dia. | Catalog Numbers | | |
|------------------------------------|-------------------------|-------------------|-------------------|---|
| Yellow nylon. | .590"-.930" (15.0-23.6) | HBL2611VY | HBL2621VY | - |
| Corrosion resistant, yellow nylon. | .590"-.930" (15.0-23.6) | HBL26CM11V | - | - |
| Black nylon. | .590"-.930" (15.0-23.6) | HBL2611VBK | HBL2621VBK | - |

Accessories on page B-51.

Flanged Inlets

Watertight Safety-Shroud IP66 SUITABILITY

| Description | Catalog Numbers | | |
|---------------------------------|------------------|------------------|---|
| Gray Valox® housing and flange. | HBL2615SW | HBL2625SW | - |

Accessories on page B-54.

Insulgrip IP20 SUITABILITY

| Description | Catalog Numbers | | |
|---|-----------------|-----------------|----------------|
| Nylon casing, back wired. | HBL2615 | HBL2625 | HBL2635 |
| Heat stabilized, gray nylon, 220° F (104° C). | HBL2615F | HBL2625F | - |

Accessories on page B-50.

Notes: For technical information on Twist-Lock® and Watertight Safety-Shroud Devices see pages B-69 and 70. For technical information on Valise plugs and connectors see page B-74.

HBLMITL - For use with Watertight Safety-Shroud receptacles, see page B-39.



Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.